



flow, stop and go®

DB125S

**

correct for DB100, DB125, DB150, DB175
DBL100, DBL125, DBL150, DBL175 taps

Data Sheet

Shop Order No.:	DB125S
"O"-Ring No.:	*****
Bag No.:	
Insert No.:	*****
Date:	*****

[bar]	0.15	0.20	0.30	0.50	1.00	1.50	2.00	3.00	4.00	5.00	6.00	Description	
[l/min]	0.25	0.86	1.78	3.09	5.41	6.65	7.70	9.40	10.88	12.18	13.31	Neostrahl	No. 1
[l/min]	0.41	0.75	1.51	2.54	4.29	5.32	5.05	5.17	5.35	5.28	5.07	PL-HC-LP 5.0L	No. 2
[l/min]	0.81	1.13	1.79	2.79	4.87	6.01	6.93	8.41	8.52	8.61	8.61	PL-HC-LP 8.0L	No. 3
[l/min]	0.81	1.04	1.69	2.64	4.32	4.74	4.10	4.20	4.21	4.07	3.83	PL-HC-LP 1.0GPM	No. 4
[l/min]	0.43	0.54	0.74	1.09	1.44	1.52	1.54	1.70	1.83	1.91	1.97	2.0L Spray	No. 5
[l/min]	0.70	0.88	1.45	2.22	3.63	4.70	5.36	6.16	5.92	6.15	6.30	Supplied PL-HC 6.0L	No. 6

Now supplied as standard with PL-HC 1.0GPM aerator/flow regulator - No. 4 above

