



flow, stop and go®

DB225C

**

Correct for DB200, DB225, DB250, DB275,
DBL200, DBL225, DBL250, DBL275 taps

Data Sheet

Shop Order No.:	DB225C
"O"-Ring No.:	*****
Bag No.:	
Insert No.:	*****
Date:	*****

[bar]	0.15	0.20	0.30	0.50	1.00	1.50	2.00	3.00	4.00	5.00	6.00	Description	
[l/min]	0.85	1.04	1.40	2.56	4.54	5.63	6.50	7.96	9.21	10.33	11.37	Neostrahl	No. 1
[l/min]	0.83	1.00	1.41	2.15	3.83	4.76	5.46	4.98	5.20	5.18	5.01	PL-HC-LP 5.0L	No. 2
[l/min]	0.66	0.81	1.25	2.41	4.18	5.21	6.01	7.35	8.41	8.34	8.53	PL-HC-LP 8.0L	No. 3
[l/min]	0.71	0.88	1.27	2.22	3.89	4.64	4.12	4.20	4.26	4.12	3.93	PL-HC-LP 1.0GPM	No. 4
[l/min]	0.53	0.63	0.77	1.03	1.37	1.42	1.44	1.57	1.69	1.77	1.82	2.0L Spray	No. 5
[l/min]	0.66	0.84	1.21	1.93	3.55	4.44	5.14	6.11	5.99	6.04	6.17	Supplied PL-HC 6.0L	No. 6
	0.11	0.13	0.21	0.50	1.02	1.37	1.67	2.13	2.52	2.78	3.11		Std.-Dev

Now supplied as standard with PL-HC 1.0GPM aerator/flow regulator - No. 4 above

